


Timken® Type E Tapered Roller Bearing Housed Unit Selection

Pillow Block: 2-Bolt Base



Dimensions in Inches Unless Otherwise Noted														Weight LBS (Approx)
Shaft Size	Part Number	B	L	A	J		Bolt Dia.	N	N ₁	H ₁	H ₂	d ₁	H	
					Min.	Max.								
1-3/16	E-P2B-TRB-1 3/16	2-3/4	6	1-7/8	4-3/4	4-13/16	1/2	9/16	19/32	7/8	3	2-1/4	1-1/2	4
1-1/4	E-P2B-TRB-1 1/4													4
1-3/8	E-P2B-TRB-1 3/8	3	7-3/8	2-1/8	5-5/8	5-7/8	1/2	5/8	3/4	1-1/8	3-3/4	2-3/4	1-7/8	7
1-7/16	E-P2B-TRB-1 7/16													7
35 mm	E-P2B-TRB-35MM													7
1-1/2	E-P2B-TRB-1 1/2	3-3/8	7-7/8	2-3/8	6-1/8	6-3/8	1/2	5/8	3/4	1-1/4	4-1/4	3-3/16	2-1/8	10
1-5/8	E-P2B-TRB-1 5/8													10
1-11/16	E-P2B-TRB-1 11/16													10
40 mm	E-P2B-TRB-40MM													10
1-3/4	E-P2B-TRB-1 3/4	3-1/2	8-7/8	2-1/2	6-7/8	7-1/8	5/8	3/4	7/8	1-5/16	4-1/2	3-7/16	2-1/4	12
1-7/8	E-P2B-TRB-1 7/8													12
1-15/16	E-P2B-TRB-1 15/16													12
2	E-P2B-TRB-2													12
45 mm	E-P2B-TRB-45MM													12
50 mm	E-P2B-TRB-50MM													12
2-3/16	E-P2B-TRB-2 3/16	3-3/4	9-5/8	2-5/8	7-5/8	7-7/8	5/8	3/4	7/8	1-1/2	5	3-3/4	2-1/2	15
55 mm	E-P2B-TRB-55MM													15
2-1/4	E-P2B-TRB-2 1/4	4	10-1/2	2-7/8	8-3/8	8-5/8	5/8	3/4	7/8	1-5/8	5-23/32	4-1/16	2-3/4	24
2-7/16	E-P2B-TRB-2 7/16													23
2-1/2	E-P2B-TRB-2 1/2													23
60 mm	E-P2B-TRB-60MM													23
65 mm	E-P2B-TRB-65MM													23
2-11/16	E-P2B-TRB-2 11/16	4-1/2	12	3	9-5/16	9-11/16	3/4	27/32	1	1-7/8	6-1/4	4-23/32	3-1/8	28
2-3/4	E-P2B-TRB-2 3/4													28
2-15/16	E-P2B-TRB-2 15/16													29
3	E-P2B-TRB-3													29
70 mm	E-P2B-TRB-70MM													28
75 mm	E-P2B-TRB-75MM	5	14	3-1/2	10-13/16	11-3/16	7/8	1	1-3/16	2-1/4	7-1/2	5-17/32	3-3/4	29
3-3/16	E-P2B-TRB-3 3/16													46
3-1/4	E-P2B-TRB-3 1/4													46
3-7/16	E-P2B-TRB-3 7/16													45
3-1/2	E-P2B-TRB-3 1/2													44
80 mm	E-P2B-TRB-80MM													46
85 mm	E-P2B-TRB-85MM													45
90 mm	E-P2B-TRB-90MM	44												

Note: All units have a 1/8" pipe thread grease fitting